

Tube Stripper for Anti-spatter Tube

Cover Stripping Cutter for Anti-spatter Tube.

Safety instructions for this product

Safety instructions, Common safety instructions for each product category and Detailed safety instructions for each product are in the end of this catalog and our website.

Model Designation (Example)

TSC
(1)

8
(2)

(1) Tube Stripper for Anti-spatter Tube

(2) Tube dia.

Code	4	6	8	10	12
O.D. (mm)	ø4	ø6	ø8	ø10	ø12
Applicable Tube type	FB0425	FB0640	FB0860	FB1075	FB1290

RoHS2 (2011/65/EU+EU2015/863) compliant

Tube Stripper for Anti-spatter Tube	Model Code
TSC	TSC4
	TSC6
	TSC8
	TSC10
	TSC12



CAD data is available
at PISCO website.



Packaging specifications
1 pc. /bag

Characteristics

Peels only the flame retardant cover like sharpening a pencil to fit the insertion dimensions of our Anti-spatter fittings.

Exclusive for PISCO's Anti-spatter Tube


Push-in fitting		Speed controller		Flow controller
Tube Fitting Anti-spatter	Tube Fitting Brass	Speed Controller Anti-spatter	Speed Controller Brass	Needle Valve Brass



Peels only the flame retardant cover without damaging the inner tube.

The transparent cover enables to check cutting progress easily.

How to use the Cutter



- (1) When cutting an Anti-spatter Tube (FB), make sure to form the cut end surface of the tube orthogonally.
 - (2) Insert an Anti-spatter Tube (FB) from tube insertion guide hole until it hits the blade.
 - (3) Insert the Anti-spatter Tube (FB) further with rotating the tube or Tube Stripper for Anti-spatter Tube clockwise until the tubing edge hits the end in the peeler.
 - (4) Keep rotating the tube (FB) or the stripper until the cover gets stripped completely, and then take out the tube from the stripper.
- *Rotate either Anti-spatter tube (FB) or Tube Stripper for Anti-spatter Tube whichever earlier to rotate.


Related products



Anti-spatter Tube

► P.108

TSC Tube Stripper for Anti-spatter Tube



Unit: mm

Model code	Applicable Tube O.D. øD	Applicable Tube type	Peeled length	Weight (g)
TSC4	4	FB0425	14.7	20
TSC6	6	FB0640	15.7	20
TSC8	8	FB0860	16.7	21
TSC10	10	FB1075	19.2	21
TSC12	12	FB1290	22.7	21